



## Autel

Garanti: 12 ay  
Bu rne ait Trkiye ii kapı teslim fiyat ve teslim sresi ieren teklifimizi almak iin [info@yursat.com.tr](mailto:info@yursat.com.tr) e-posta adresine baŐuru yapabilir ya da ayrıntılı bilgi iin +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz. **Autel** Markası, tedarik sresi iin ltfen bizimle iletiŐime geiniz.

*Firmamız Autel Trkiye Distribtr veya temsilcisi deėildir. Firmamız sipariŐ durumunda, belirtilen rnlerde sadece Orjinal ve yeni rn teklifi sunmaktadır. Bu sitede gsterilen zel marka adları ve ticari markalar ilgili sahiplerinin mlkiyetindedir, talep durumunda kaldırılmaktadır.*

| rn                         | Aıklama  |
|------------------------------|---|
| <a href="#">VI10010702</a>   | VALV.1" ATT.VITE CORTO 24VDC S.10C DIRITTO BQ AE1825B1020 KIT 1 SCREW VALVE+PILOT+COIL(P52) 24VDC (S) AE1825B1020 S10 Thread Connection 1" Valve AE1825B1, short inlet. Valve equipped with Pilot Group Sys.10 (coil voltage 24V DC). |
| <a href="#">01000ARC831</a>  | UNITA' REMOTA RPA-612 S12 8 USCITE RACC. CURVI + HEATER   |
| <a href="#">01000ARD501</a>  |   |
| <a href="#">01000GF0401</a>  |   |
| <a href="#">01000GF1201</a>  |   |
| <a href="#">01000MP0201</a>  |   |
| <a href="#">01000NS2001</a>  |   |
| <a href="#">01000PBD061</a>  |   |
| <a href="#">01000S00301</a>  |   |
| <a href="#">01000SV0404C</a> |   |
| <a href="#">01000SV0504C</a> |   |
| <a href="#">01000SV0C04C</a> |   |
| <a href="#">ae1440b</a>      |   |

|                              |
|------------------------------|
| <a href="#">ae1440i06</a>    |
| <a href="#">ae1440i06pma</a> |
| <a href="#">ae1440i08</a>    |
| <a href="#">ae1440r</a>      |
| <a href="#">ae1450b</a>      |
| <a href="#">ae1450i08</a>    |
| <a href="#">AE1460B020</a>   |
| <a href="#">ae1460i10</a>    |
| <a href="#">ae1460i12</a>    |
| <a href="#">ae1475i12</a>    |
| <a href="#">ae1818b</a>      |
| <a href="#">ae1822b</a>      |
| <a href="#">ae1825b0</a>     |
| <a href="#">AE1825ITS</a>    |
| <a href="#">ae1825i06</a>    |
| <a href="#">ae1825r</a>      |
| <a href="#">ae1840i06</a>    |
| <a href="#">ae1840i08</a>    |
| <a href="#">ae2440</a>       |
| <a href="#">ae2440i0</a>     |
| <a href="#">ae2440i06</a>    |
| <a href="#">ae2440i06pma</a> |
| <a href="#">ae2440i08</a>    |
| <a href="#">ae2440r</a>      |
| <a href="#">ae2450b</a>      |
| <a href="#">ae2450i08</a>    |
| <a href="#">ae2450i10</a>    |
| <a href="#">ae2460b</a>      |
| <a href="#">ae2460i10</a>    |
| <a href="#">ae2460i12</a>    |
| <a href="#">ae2475i12</a>    |
| <a href="#">ae2818b</a>      |
| <a href="#">ae2822b</a>      |
| <a href="#">ae2825b0</a>     |
| <a href="#">ae2825b1</a>     |
| <a href="#">ae2825i06</a>    |

|                               |
|-------------------------------|
| <a href="#">ae2825r</a>       |
| <a href="#">AE2840I06.</a>    |
| <a href="#">AE2840I08.</a>    |
| <a href="#">ae2840i0</a>      |
| <a href="#">ae2840i06</a>     |
| <a href="#">ae2840i08</a>     |
| <a href="#">Ats-25</a>        |
| <a href="#">Ats-25e</a>       |
| <a href="#">Ats-45</a>        |
| <a href="#">Ats-45e</a>       |
| <a href="#">Ats-i</a>         |
| <a href="#">AU-304000900</a>  |
| <a href="#">Br1led</a>        |
| <a href="#">CE99FFC0710</a>   |
| <a href="#">Cm-e01</a>        |
| <a href="#">Cm-s01</a>        |
| <a href="#">Cpe</a>           |
| <a href="#">D100-1l</a>       |
| <a href="#">D100-2l</a>       |
| <a href="#">D100-e</a>        |
| <a href="#">D100-s</a>        |
| <a href="#">D52 fuel</a>      |
| <a href="#">D52 h2o</a>       |
| <a href="#">D52 oil</a>       |
| <a href="#">D52 voltmeter</a> |
| <a href="#">D52-c</a>         |
| <a href="#">D52-gps</a>       |
| <a href="#">Dpf 15e</a>       |
| <a href="#">Dpf 1-c</a>       |
| <a href="#">Dpf 20</a>        |
| <a href="#">Dpf 20 reg</a>    |
| <a href="#">Dpf 4-20</a>      |
| <a href="#">Dr-35</a>         |
| <a href="#">Eco</a>           |
| <a href="#">FQ 84299</a>      |
|                               |

|   |
|---|
| <a href="#">Ge-a01</a>                            |
| <a href="#">Ge-m01</a>                            |
| <a href="#">IN5024AT02</a>                        |
| <a href="#">Led_rgb</a>                           |
| <a href="#">Ma810</a>                             |
| <a href="#">MD60KIT</a>                           |
| <a href="#">Mnt</a>                               |
| <a href="#">Mnt16io</a>                           |
| <a href="#">Mnt8io</a>                            |
| <a href="#">Mvp_20</a>                            |
| <a href="#">Pdp2</a>                              |
| <a href="#">Pf4</a>                               |
| <a href="#">pm25</a>                              |
| <a href="#">pm40</a>                              |
| <a href="#">pm40b</a>                             |
| <a href="#">pm50</a>                              |
| <a href="#">pm50b</a>                             |
| <a href="#">pmb</a>                               |
| <a href="#">PT001121C</a>                         |
| <a href="#">PT004121C</a>                         |
| <a href="#">PT006121C</a>                         |
| <a href="#">PT009127EX+RC99521301404+PT00A036</a> |
| <a href="#">Pvf2</a>                              |
| <a href="#">Pwm2</a>                              |
| <a href="#">Rdp-1</a>                             |
| <a href="#">Rp-02</a>                             |
| <a href="#">Rp-04 + gdm-1</a>                     |
| <a href="#">Rp-04 + sdm-1</a>                     |
| <a href="#">RPB_612/12</a>                        |
| <a href="#">Rte-24-12-20a</a>                     |
| <a href="#">Rte-72-12-30a</a>                     |
| <a href="#">Sa-01</a>                             |
| <a href="#">Sa-01s</a>                            |
| <a href="#">Sa-05</a>                             |
| <a href="#">Sa-10</a>                             |
| <a href="#">Sa-12c</a>                            |

|  |  |
|--|--|
| <a href="#">Sta43/57/70</a>              |  |
| <a href="#">Str</a>                      |  |
| <a href="#">SYS10</a>                    |  |
| <a href="#">SYS8</a>                     |  |
| <a href="#">Tr2825k06</a>                |  |
| <a href="#">VL000010ZZ10MHT</a>          |  |
| <a href="#">VL000015ZZ05M</a>            |  |
| <a href="#">VL00C011B</a>                |  |
| <a href="#">VL00C040V</a>                |  |
| <a href="#">VL00C105</a>                 |  |
| <a href="#">VL03000004</a>               |  |
| <a href="#">VL10000006</a>               |  |
| <a href="#">VL10000020</a>               |  |
| <a href="#">VL10010513</a>               |  |
| <a href="#">VL10020704</a>               |  |
| <a href="#">VL10050701</a>               |  |
| <a href="#">VL10200001</a>               |  |
| <a href="#">VL10220701</a>               |  |
| <a href="#">VL15011702M</a>              |  |
| <a href="#">VL15021702M</a>              |  |
| <a href="#">VL15041701M</a>              |  |
| <a href="#">VL151010112M7</a>            |  |
| <a href="#">VL15104000M6</a>             |  |
| <a href="#">VL201000009</a>              |  |
| <a href="#">VL25100000</a>               |  |
| <a href="#">3" VALVES</a>                | Can you send me your price list for the spare parts?             |
| <a href="#">245BF01</a>                  |  |
| <a href="#">245BF01</a>                  | POS: 6 MODEL: AE2450W  |
| <a href="#">245BF01 DIYAFRAM POS: 7</a>  |  |
| <a href="#">245BF01 / POS: 11</a>        |  |
| <a href="#">245BF01 DIYAFRAM POS: 12</a> |  |
| <a href="#">VL000020ZZ050</a>            | AUTEL KIT DIAPHRAGMS + SPRINGS FOR 2" VALVES                     |
| <a href="#">AE1825B1</a>                 | AUTEL 1" STANDARD VALVE (SHORT INLET) 24VDC                      |
| <a href="#">AE1440B</a>                  |  |
| <a href="#">AE1440B repair kit</a>       |  |
|  | MD75KIT Diaphragms Kit for 2"1/2 and 3" valves. Main diaphragm + |

|  |  |
|--|--|
| <a href="#">KIT MEMBRANE PER VALVOLE 3</a>   | small diaphragm  |
| <a href="#">VL15011702M</a>  | VALV.1.5" ATT.VITE 24VDC S.10C DOPPIO STADIO AE1440B020 M.P. AE1440B020 Thread Conn. 1"1/2 Double Stage Valve AE1440B, with Pilot Group 24V DC |
| <a href="#">VL00A052C01</a>  |  |
| <a href="#">PT009106</a>   | AUTEL Pilot-valve System 10 for Pulse Jet valves   |
| <a href="#">VL00A028B</a>  | AUTEL 3/4" ALLUMINUM COVER   |
| <a href="#">ECOSERIAL-P3</a>   | S/N: 16102839500002 with amplifier (S/N: 507/26634/63  |
| <a href="#">VL15F00001 valve kit</a>   | AEAUTEL 70003639   |
| <a href="#">AZ440W solenoid kit</a>  | AEAUTEL 70003638   |
| <a href="#">Coil for AZ440W 110V 50/60 HZ4</a>   | AEAUTEL 70003637   |
| <a href="#">IN5230AT02</a>   | BC10 220VAC AUTEL solenoid coil 17W for Sys10 Pilot 220VAC   |
| <a href="#">AE1450B 24/DC</a>  | AUTEL impulse diaphragm valve 2" 24VC  |
| <a href="#">VL00D003</a>   | AUTEL MOLLA PER VALVOLA DA 3 GAS 3 SPIRE CORDA=2MM DE=51 LL=29 SPRING FOR 3 VALVE GAS 3 COILS Part 9   |
| <a href="#">VL00D013</a>   | AUTEL MOLLA A COMPR.FILO 1.2 FD Si Cr LL.28.6MM DE=16 DI= LL=28.6 ST=7,5 Part 8  |
| <a href="#">VL00C011VKIT</a>   | AUTEL VITON Membrane Kit for 2" Valves. Kit includes: - Main diaphragm in VITON - O-ring - Spring  |
| <a href="#">Jet Pulse Vana DN 65 Diafram</a>   | need for spare parts   |
| <a href="#">DPF-20</a>   | AUTEL Differential Pressure Sensor DPF-20, range -99/+999 mmH2O, input voltage AC  |
| <a href="#">DPF-20, 4-20mA, RS485</a>  | AUTEL Differential Pressure Sensor DPF-20, range -99/+999 mmH2O, 4-20 mA, input voltage AC, RS485  |
| <a href="#">VI00c101 Diaphragm 1" For 1" Valves</a>  |  |
| <a href="#">Tcp-2yr</a>  | 2 YEAR UPDATE FOR DS708  |
| <a href="#">Ae1440b020</a>   |  |
| <a href="#">Ms908</a>  | SOFTWARE   |
| <a href="#">Ts501</a>  | MAXI TPMS TS501  |
| <a href="#">Ae1460b</a>  |  |
| <a href="#">Ae2818b Membran Ventil 4b 3/4</a>  |  |
| <a href="#">VI00c101 Membrana 1" Profilo A Pinna Foro 1,4mm1" Diaphragm (Springless)1" Diaphragms For Ae1825b1</a> |  |
| <a href="#">Mn1499095</a>  |  |
| <a href="#">VI00c041</a>   |  |
| <a href="#">VI00c040</a>   |  |
| <a href="#">For Box Sp04-020 Valvola</a>   |  |
| <a href="#">Ae2822b000 Std Diaphragm.</a>  |  |
| <a href="#">Ms905</a>  | MAXISYS MINI   |

|  |                            |
|--|----------------------------|
| <a href="#">Maxisys Ms908 Pro</a>  |                            |
| <a href="#">Pt009127ex</a>   |                            |
| <a href="#">Valve Repair Kit Ae1440b020</a>  |                            |
| <a href="#">17365 1 1/2 "diaphragm Valve</a>                                       |                            |
| <a href="#">Rpb-612/5 Remote Pilot Box-</a>  |                            |
| <a href="#">Ms908p</a>   | MAXISYS PRO W/VCI (J-2534) |
| <a href="#">Ae1825r Valvola Con Gruppo Pilota</a>                                  |                            |
| <a href="#">Pt009127ex Pilota S8/2 Per Clip 2 Vie Inn. Femmina 1/4" Bsp , Atex</a> |                            |
| <a href="#">Ae1825bo226 1quot;</a>   |                            |
| <a href="#">VI00a005</a>   |                            |
| <a href="#">Ts601</a>  | MAXI TPMS                  |
| <a href="#">Pt00a036 Clip Pilota Sistema 8 Remotoclip System8 Pilot</a>            |                            |
| <a href="#">VI000020zz050</a>  |                            |
| <a href="#">Pt00a036</a>   |                            |
| <a href="#">For Box Sp12-020 Valvola</a>   |                            |
| <a href="#">??2440? Valvova</a>  |                            |
| <a href="#">01000pbd041</a>  |                            |
| <a href="#">Ae2840itlf Solenoid Valve</a>  |                            |
| <a href="#">Diaphragm Kit For Valve Ae2460b</a>                                    |                            |
| <a href="#">Maxisys Ms908cv</a>  |                            |
| <a href="#">VI15051701m</a>  |                            |
| <a href="#">Str-3 Cyclic Generator 90-240 Vac</a>                                  |                            |
| <a href="#">Box Sp12-020 Controller</a>  |                            |
| <a href="#">VI15000003m</a>  |                            |
| <a href="#">Tf02 B07c</a>  |                            |
| <a href="#">Ae 1450 B 2quot;</a>   |                            |
| <a href="#">Ae2825r000 Diaphragm For Valve</a>                                     |                            |
| <a href="#">Sq10.2 F10 Ap 203</a>  |                            |
| <a href="#">??2840itlf Valvova</a>   |                            |
| <a href="#">Dpf-20 Versorgung: 110/220 Vac; Bereich - 99+999 Mmh20</a>             |                            |
| <a href="#">V 24 Ac Valveonly Valve, Without Coil</a>                              |                            |
| <a href="#">Ae1460b020 24 Vdc</a>  |                            |
| <a href="#">Kit Diaphragms For 1 1/2quot; Double Stage Valve</a>                   |                            |
| <a href="#">Probe Rp04 + Controller Gdm1</a>                                       |                            |

|   |  |
|---|--|
| <a href="#">M/D40sht VI00c040v Reparateursatzht Diaphragm 1 1/2" Kit (Viton+ptfe)</a> |  |
| <a href="#">Md25kit Repair Kit</a>  |  |
| <a href="#">Box Sp04-020 Controller</a>   |  |
| <a href="#">Rpb-612/12 Remote Pilot Box Rpb-612/12, Ce Certified, With 12 Outputs</a> |  |
| <a href="#">Probe Rp04 + Controller Sdm1</a>  |  |
| <a href="#">Ae1440b225 11/2quot;</a>  |  |
| <a href="#">Ae1825r115</a>  |  |
| <a href="#">Ae 1450 B 2quot; Part No: 10 B</a>  |  |
| <a href="#">M/D25</a>   |  |
| <a href="#">Box Spv12-020 Pneumatic Valve Control Unit</a>                            |  |
| <a href="#">Md25 1quot;</a>   |  |
| <a href="#">Diaphragms Kit For Autel Valve Ae1450its</a>                              | including 2" diaphragm, 3/4" diaphragm and 2 springs |
| <a href="#">Ae1450i10</a>   |  |
| <a href="#">Valve Repair Kit Md25kit Ae1825b1020</a>                                  |  |
| <a href="#">VI00c105 Diaphragm 3/4" For Small Valves</a>                              |  |
| <a href="#">VI25010701</a>  |  |
| <a href="#">VI00d002v</a>   |  |
| <a href="#">Gc12p</a>   |  |
| <a href="#">Ae1825b0225 1quot;</a>  |  |
| <a href="#">Ae 1450 B 2quot; Part No: 8(VI00d002)</a>                                 |  |
| <a href="#">Ventil Pulse1"1/2</a>   |  |
| <a href="#">Coil 24vdc For Pilot Sys 10</a>   |  |
| <a href="#">Dpf-20 Druckdifferenzmesser</a>   |  |
| <a href="#">Rc99521301404</a>   |  |
| <a href="#">Viton Diaphragm 1quot; + Oring + Spring For Valve Ae1825b</a>             |  |
| <a href="#">Dpf15e Sensore Di Pressione Differenziale</a>                             |  |
| <a href="#">Ae1440bo226 1 1/2</a>   |  |
| <a href="#">Ae 1450 B 2quot; Part No 9</a>  |  |
| <a href="#">Ds708</a>   | SCAN TOOL  |
| <a href="#">Ae2440b</a>   |  |
| <a href="#">Probe Rp04</a>  |  |
| <a href="#">Ds708tpr</a>  | *DS708/TS401 PROMO                                   |
| <a href="#">VI10210708</a>  |  |
| <a href="#">Rpa/Rpb</a>   |  |



|   |  |
|---|--|
| <a href="#">VI10020706 Coil</a>           |  |
| <a href="#">Ae 1460b230 ( VI25050701)</a> |  |
| <a href="#">Mf2534</a>                    | MAXIFLASH PRO  |
| <a href="#">Ae1450its</a>                 | (coil voltage to beconfirmed, blow pipes short and plain), PEASE CONFIRM IF THE VALVE WILL BE ASSEMBLED ON 8" OR 10" HEADER TANK   |
| <a href="#">VI00c101</a>                  |  |
| <a href="#">Ae1825b1</a>                  |  |
| <a href="#">VI000030zz050</a>             | KIT MEMBRANE PER VALVOLE 3 KIT DIAPHRAGMS FOR 2 1/2" AND 3" INTEGRATED VALVE 3" Diaphragms Kit suitable for 2,5" Double Stage Integrated Valves. Kit includes: 3"Diaphragm+3/4"Diaphragm |
| <a href="#">VI00c003ixef</a>              |  |
| <a href="#">Ae1820b225 3/4quot;</a>       |  |
| <a href="#">Ae1820bo226 3/4quot;</a>      |  |
| <a href="#">VI00c041v</a>                 |  |
| <a href="#">Ae1450 B</a>                  |  |
| <a href="#">VI000020zz060</a>             |  |