



## Branson

Garanti: 12 ay

Bu ¼r¼ne ait T¼rkiye ii kapı teslim fiyat ve teslim s¼resi ieren teklifimizi almak iin [info@yursat.com.tr](mailto:info@yursat.com.tr) e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi iin +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz.

**Branson** Markası, tedarik s¼resi iin l¼tfen bizimle iletiŐime geiniz.

*Firmamız Branson T¼rkiye Distrib¼t¼r¼ veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen ¼r¼nlerde sadece Orjinal ve yeni ¼r¼n teklifi sunmaktadır. Bu sitede g¼sterilen ¼zel marka adları ve ticari markalar ilgili sahiplerinin m¼lkiyetindedir, talep durumunda kaldırılmaktadır.*

¼r¼n	Aıklama
<a href="#">Kit40/500/Hand</a>	Kit Low Power / Lpx / 40kHz / 550W /HAT
<a href="#">Kit40/500/Pt</a>	LPX - Kit Low Power 40kHz 550W Pistol grip (PT)
<a href="#">101-132-1806</a>	Ultrasonic generator DCX S series: 0.80 DCXs 40VRT Working frequency 40 kHz, Power output 800 watts, with automatic frequency control and variable Amplitude adjustment as well Voltage stabilization up to ± 15% mains input fluctuations. An I / O interface is available for communication with a PLC. The integrated LCD display with function keys as well as the Ethernet interface with the integrated web software enable the query of system information, diagnosis as well as the parameterization of generator functions. With the assembly kit, the generator can be variably mounted in the control cabinet (vertical). (For technical data see data sheet)
<a href="#">101-135-068</a>	Converter 4 TP (plate mount) piezoelectric transducer to convert the electrical Energy in mechanical Vibrations
<a href="#">20527000</a>	Vectron BRA 400-034-BF1
<a href="#">109-074-939</a>	
<a href="#">Modell LPX</a>	Ultrasonic generator Working frequency 40 kHz. The LPX (Low Power X Series) model has the operating modes Continuous noise, time and energy and optionally via a metal contact Shutdown. The output power is 550 watts and is shown on an LCD display. The parameters are entered via the LCD display and the corresponding function keys. The adjustable welding time is 50 ms - 9.99 seconds, the welding energy 1 - 9999 joules.
<a href="#">159-135-133</a>	Pistol grip PT 480 with built-in converter attached HF cable and push button for switching the ultrasound on and off (takes precedence over the time setting on the generator)

<a href="#">101-135-049</a>	Converter 922JA
<a href="#">Handheld ultrasonic welding machine LPX model,</a>	40Khz. 550Watt. Handgun and Tit. Complete including Welding Tip. 1 spare Welding Tip Tit. 40kHz (Model EST21274)
<a href="#">011-CXX-206</a>	HF Cable SHV/SHV(W)
<a href="#">Screw</a>	Screw: EDP 100-098-120 wie J919-709-00003
<a href="#">Spezial Booster</a>	Booster wie 821-303-Y16N002; 30KHz; material Titan
<a href="#">101-135-081R</a>	Model CR-30 converter with SHV connector
<a href="#">011-003-494</a>	JPGA/SHV > MS RF-Cable app. 7,50m long
<a href="#">101-135-068R</a>	Model 4TP Converter, 40 kHz, Plate Mount
<a href="#">EST11388</a>	
<a href="#">308-010-021</a>	
<a href="#">312-004-021</a>	
<a href="#">302-001-021</a>	
<a href="#">100146678</a>	
<a href="#">Model: 4mb4</a>	
<a href="#">318-002-021</a>	
<a href="#">109-044-082</a>	
<a href="#">922ra</a>	CONVERTER
<a href="#">101-135-049</a>	CONVERTER FOR 920IW 922JA
<a href="#">109-041-160</a>	WELDING BOOSTER 1:1 GREEN AT 20KHZ
<a href="#">308-004-021</a>	
<a href="#">Aku Cover Screws</a>	
<a href="#">317-001-021</a>	
<a href="#">310-004-021</a>	
<a href="#">306-004-021</a>	
<a href="#">Cpx-952-338r</a>	2.5Gal.UltrsncCleanr w/Dig.Timr Heater, Degas&Temp.Monitor
<a href="#">312-006-021</a>	
<a href="#">943bc</a>	POWER SUPPLY
<a href="#">4tr 101-135-042</a>	
<a href="#">M8800</a>	CLEANER

<a href="#">Cpx-952-216r</a> <a href="#">932as 1210066</a>	3/4 Gallon Ultrasonic Cleaner 120V
<a href="#">159135257</a>	CONVERTER
<a href="#">000-951-030r</a>	Ultrasonic Pipette Cleaner Unheated 115 volts
<a href="#">Cpn-908-014</a>	IC Ultrasonic Cleaner, 230 V 40 kHz
<a href="#">100-146-674</a>	POWER SUPPLY MODEL LB90 FLASH 8
<a href="#">101-135-059r</a>	CONVERTER CJ20
<a href="#">920d</a>	POWER SUPPLY
<a href="#">316-016-021</a>	
<a href="#">318-004-021</a>	
<a href="#">100-240-392</a>	
<a href="#">610-004-021</a>	
<a href="#">S8340-18</a>	GENERATOR ULTRASONIC CLEANING 220V 750WATT
<a href="#">312-012-021</a>	
<a href="#">304-008-021</a>	
<a href="#">920bca</a>	POWER SUPPLY
<a href="#">Cpx-952-316r</a>	
<a href="#">Dc480b</a>	POWER MODULE ULTRASONIC COMPACT DIGITAL 40:0:8
<a href="#">101-132-2070</a>	POWER SUPPLY DCXS 40 800 WATT RACK MOUNT
<a href="#">306-006-021</a>	
<a href="#">101-240-035</a>	
<a href="#">308-001-021</a>	
<a href="#">109-122-003</a>	
<a href="#">90 Degrees Socket For Rf Cable</a>	
<a href="#">608-001-021</a>	
<a href="#">314-001-021</a>	
<a href="#">318-008-021</a>	
<a href="#">101-135--060</a>	CONVERTER
<a href="#">Cpn-908-012</a>	IC Ultrasonic Cleaner, 208 V 40 kHz
<a href="#">606-001-021</a>	
<a href="#">100-240-384</a>	

<a href="#">Cpx-952-216r</a>	
<a href="#">304-006-021</a>	
<a href="#">Edp014-Cxx-808</a>	TYPE 7400 CUTTING BLADE HORN
<a href="#">444-022-021</a>	
<a href="#">Cpx-952-518r</a>	2.5 Gallon Ultrasonic Cleaner 120V
<a href="#">900b</a>	POWER SUPPLY
<a href="#">306-009-021</a>	
<a href="#">000-914-606</a>	Ultrasonic Cleaner, 50/60Hz
<a href="#">Cpx-952-517r</a>	2.5 Gallon Ultrasonic Cleaner 120V
<a href="#">316-017-021</a>	
<a href="#">101-132-1805</a>	
<a href="#">Cpn-908-024</a>	Integrated Cleaner, 230 V 40 kHz
<a href="#">600-001-021</a>	
<a href="#">100-187-013</a>	
<a href="#">605-002-021</a>	
<a href="#">069210001</a>	MOTOR
<a href="#">Cpx-952-817r</a>	Ultrasonic Cleaner, MH, 5.5gal
<a href="#">947bca</a>	POWER SUPPLY
<a href="#">3510</a>	WASHER
<a href="#">101-063-569</a>	PC BOARD CE INSTALLATION KIT
<a href="#">Cpx-952-317r</a>	1-1/2Gal.Ultrsnc Cleanr w/Mech. Timr&Heatr, 11.5"x6"x6"ID
<a href="#">Edp No: 101-149-080</a>	
<a href="#">101-132-661</a>	POWER SUPPLY
<a href="#">613-005-021</a>	
<a href="#">308-008-021</a>	
<a href="#">Hg420</a>	
<a href="#">101-149-064</a>	
<a href="#">316-002-021</a>	
<a href="#">011-530-006</a>	
<a href="#">308-006-021</a>	

<a href="#">312-002-021</a>	
<a href="#">609-010-021</a>	
<a href="#">302-002-021</a>	
<a href="#">2.50 Dcxs 20hor/ 101-132-1793</a>	
<a href="#">Cpx-952-337r</a>	1.5 Gallon Ultrasonic Cleaner 230V
<a href="#">304-004-021</a>	
<a href="#">Dc22</a>	POWER MODULE
<a href="#">606-002-021</a>	
<a href="#">Cpn-908-023</a>	Integrated Cleaner, 230 V 25 kHz
<a href="#">101-063-891</a>	
<a href="#">Cpx-952-217r</a>	3/4Gal.Ultrsnc Cleanr w/Mech. Timer&Heater, 9.5"x5.5"x4"ID
<a href="#">S7025-36</a>	ULTRASONIC CLEANER POWER SUPPLY 1500WATT
<a href="#">310-001-021</a>	
<a href="#">603-002-021</a>	
<a href="#">Edp No: 101-135-067</a>	
<a href="#">Cpx-952-538r</a>	2.5 Gallon Ultrasonic Cleaner 230V
<a href="#">Cpn-908-021</a>	Integrated Cleaner, 208 V 25 kHz
<a href="#">100-222-028</a>	KEY/DISPLAY BD
<a href="#">Fc6182512c</a>	IMMERSION HTR
<a href="#">Pm112</a>	GENERATOR
<a href="#">0005-1, Sonotrode 20 Khz, Typ Rectangular</a>	
<a href="#">609-001-021</a>	
<a href="#">302-004-021</a>	
<a href="#">1510r-Mt</a>	
<a href="#">100244085r</a>	POWER SUPPLY
<a href="#">S852524</a>	GENERATOR
<a href="#">715-001-021</a>	
<a href="#">308-012-021</a>	
<a href="#">316-006-021</a>	
<a href="#">101-134-108</a>	ACTUATOR 2000-SERIES 100PSI 690KPA 6.89BAR

<a href="#">109-041-174</a>	BOOSTER T1 40KHZ SOLID MOUNT BLACK
<a href="#">101-160-902</a>	
<a href="#">4mb4</a>	PWR SUPPLY MOD
<a href="#">Cpx-952-318r</a>	1.5 Gallon Ultrasonic Cleaner Digital Timer, Heater
<a href="#">306-002-021</a>	
<a href="#">101-147-037</a>	
<a href="#">101-063-212</a>	
<a href="#">S834012</a>	POWER SUPPLY
<a href="#">610-001-021</a>	
<a href="#">611-001-021</a>	
<a href="#">314-010-021</a>	
<a href="#">600-009-021</a>	
<a href="#">901aes</a>	ACTUATOR
<a href="#">902r</a>	CONVERTER ULTRASONIC
<a href="#">316-012-021</a>	
<a href="#">312-008-021</a>	
<a href="#">91obca</a>	POWER SUPPLY 117V 101-132-265 LA01062592
<a href="#">101-147-053</a>	HORN RESONATOR 1.5INCH
<a href="#">S8025-18</a>	POWER SUPPLY ULTRASONIC 230V 50/60HZ 5.5AMP
<a href="#">318-006-021</a>	
<a href="#">609-003-021</a>	
<a href="#">011-003-069wrf</a>	
<a href="#">014cxx808</a>	HORN
<a href="#">159-132-2007</a>	
<a href="#">M/Mh 1800-8800</a>	
<a href="#">144-100-006</a>	DRIVE 10HP
<a href="#">B-400-R</a>	ULTRASONIC CLEANER 230V R12 31.5X22X46IN 9GA 40KHZ
<a href="#">921-Aes</a>	ULTRASONIC WELDER CONTROLLER
<a href="#">Branson 2000 Iw+</a>	
<a href="#">314-008-021</a>	
<a href="#">101-135-042r</a>	

<a href="#">Cpx-952-137r</a>	1/2Gal.Ultrsnc Cleanr w/Mech. Timer&Heater, 5.5"x6"x4"ID, 230V
<a href="#">613-003-021</a>	
<a href="#">607-001-021</a>	
<a href="#">101-132-1791</a>	
<a href="#">921ae</a>	CONVERTER
<a href="#">Ups480</a>	
<a href="#">Cpx3800h-E</a>	
<a href="#">628-008-021</a>	
<a href="#">Pc76200</a>	CONTROL BOARD PC76200
<a href="#">611-003-021</a>	
<a href="#">Cpn-908-011</a>	IC Ultrasonic Cleaner, 208 V 25 kHz
<a href="#">2000xdt 15:3.3</a>	
<a href="#">000-951-430</a>	Ultrasonic Pipette Cleaner
<a href="#">316-001-021</a>	
<a href="#">159-132-1400</a>	POWER SUPPLY 15AMP 400VAC 50/60HZ 6000W
<a href="#">Pc620-1</a>	ULTRASONIC PIPET CLEANER 1.5AMP 117V 50/60HZ
<a href="#">628-006-021</a>	
<a href="#">436-005-021</a>	
<a href="#">Model: 2800</a>	
<a href="#">4tp Edp:101-135-068</a>	
<a href="#">Cpn-952-138</a>	Ultrasonic Cleaner w/Dig.Timer, Heater&Degas, & Temp.Monitor
<a href="#">1510-Dth</a>	
<a href="#">Cpx-952-118r</a>	Ultrsnc.Clnr.w/Dig.Timer, Heater Degas&Temp.Monitor, 1/2Gal., 120V
<a href="#">306-003-021</a>	
<a href="#">101-132-1798</a>	
<a href="#">Edm :101-135-042r</a>	
<a href="#">101-135-066</a>	CONVERTER FOR DIGITAL SONIFIER MODEL 102
<a href="#">520-001-021</a>	
<a href="#">603-001-021</a>	

<a href="#">612-001-021</a>	
<a href="#">101-149-056</a>	BOOSTER TITANIUM GREEN 1:1
<a href="#">00005-1, Sonotrode 20 Khz (Ö;Hnlich Wie Ge 121887)</a>	
<a href="#">Cpx-952-838r</a>	5.5Gal.UltrsncCleanr w/Dig.Timr Heatr, Degas&Temp.Monitr, 230V
<a href="#">600-011-021</a>	
<a href="#">108-135-044</a>	CONVERTER 40MZ
<a href="#">Cpx-952-218r</a>	3/4Gal.Ultrsnc Cleanr w/Dig.Tmr Heatr, Degas&Temp.Monitor, 120V
<a href="#">Cpx-952-516r</a>	2.5 Gallon Ultrasonic Cleaner 120V
<a href="#">Cpn-908-013</a>	IC Ultrasonic Cleaner, 230 V 25 kHz
<a href="#">Cpx-952-136r</a>	1/2 Gal.Ultrsnc Cleanr w/Mech. Timer, 5.5"x6"x4"ID, 230V
<a href="#">101&amp;#8208;135&amp;#8208;042</a>	
<a href="#">Cpx-952-238r</a>	3/4Gal.Ultrsnc Cleanr w/Dig.Ti mr, Heatr, Degas&Temp.Monitr, 230V
<a href="#">0.80 Cdxs 40bdc</a>	
<a href="#">95940657</a>	
<a href="#">020-600-025l</a>	
<a href="#">310-006-021</a>	
<a href="#">Cpn-952-137</a>	1/2Gal.Ultrasonic Heater w/Mech Timer & Heater
<a href="#">602-001-021</a>	
<a href="#">304-002-021</a>	
<a href="#">101-135-042 (Ex101-135-042r)</a>	
<a href="#">302-006-021</a>	
<a href="#">308-014-021</a>	
<a href="#">310-012-021</a>	
<a href="#">Cpx-952-816r</a>	5.5Gal.UltrsncCleanr w/Mech.Tmr 19.5"x11"x6"ID, 120V
<a href="#">101-135-081r</a>	
<a href="#">604-001-021</a>	
<a href="#">314-003-021</a>	
<a href="#">752-005-021</a>	



<a href="#">607-002-021</a>	
<a href="#">312-010-021</a>	
<a href="#">316-004-021</a>	
<a href="#">601-001-021</a>	
<a href="#">314-004-021</a>	
<a href="#">308-002-021</a>	
<a href="#">424-023-021</a>	
<a href="#">910b</a>	POWER SUPPLY
<a href="#">922ja Converter</a>	101-135-049 piezoelectric sound transducer to convert electrical energy into mechanical vibrations
<a href="#">109-169-655</a>	
<a href="#">101-149-099</a>	BOOSTER 20KHZ SOLID MOUNT BLACK
<a href="#">304-001-021</a>	
<a href="#">611-005-021</a>	
<a href="#">306-001-021</a>	
<a href="#">8510r-Dth</a>	CLEANER 99-MINUTE CYCLE 70DEG/C 7.5A 940W 1POLE
<a href="#">011-003-494I2(Ex 100-240-397)</a>	
<a href="#">310-008-021</a>	
<a href="#">613-012-021</a>	
<a href="#">600-007-021</a>	
<a href="#">Cpn-952-237</a>	3/4 Gallon Ultrasonic Cleaner Mechanical Timer, Heater 230 V
<a href="#">628-010-021</a>	
<a href="#">605-001-021</a>	
<a href="#">019200119</a>	DRIVE
<a href="#">Btc 200</a>	
<a href="#">318-001-021</a>	
<a href="#">Cpx-952-236r</a>	3/4Gal.Ultrsnc Cleanr w/Mech. Timer, 9.5"x5.5"x4"ID, 230V
<a href="#">314-002-021</a>	
<a href="#">000-951-330r</a>	Ultrasonic Pipette Cleaner Heated 115V
<a href="#">312-001-021</a>	
<a href="#">000-951-130</a>	Ultrasonic Pipette Cleaner

<a href="#">Cpx-952-818r</a>	ULTRASONIC BENCH TOP CLEANER W/HEATER 5.5GALLONS
<a href="#">2510á;</a>	
<a href="#">101-240-182d Ex.(159-240-182)</a>	
<a href="#">302-008-021</a>	
<a href="#">Solid Mount 20 Khz Gold (Ti), 101-149-097d</a>	
<a href="#">109-067-612</a>	
<a href="#">316-010-021</a>	
<a href="#">536-005-021</a>	
<a href="#">316-014-021</a>	
<a href="#">306-008-020</a>	
<a href="#">613-001-021</a>	
<a href="#">Ups 10kva, 15amp</a>	
<a href="#">011-004-030(Ex100-240-392)</a>	
<a href="#">620-001-021</a>	
<a href="#">609-002-021</a>	
<a href="#">612-005-021</a>	
<a href="#">314-012-021</a>	
<a href="#">125-063-1002</a>	
<a href="#">Cpx-952-537r</a>	2.5 Gallon Ultrasonic Cleaner Mechanical Timer, Heater 230 V
<a href="#">310-010-021</a>	
<a href="#">Br -1004</a>	
<a href="#">600-014-021</a>	
<a href="#">604-002-021</a>	
<a href="#">310-002-021</a>	
<a href="#">413-001-021</a>	
<a href="#">316-008-021</a>	
<a href="#">Edp 101 149 093</a>	
<a href="#">Cpx-952-138r</a>	1/2 Gallon Ultrasonic Cleaner Digital Timer, Heater, 230V
<a href="#">101-149-080</a>	
<a href="#">302-009-021</a>	