

## Byk Gardner

Garanti: 12 ay  
Bu ¼r¼ne ait T¼rkiye i¼i kapı teslim fiyat ve teslim s¼resi i¼eren teklifimizi almak i¼in [info@yursat.com.tr](mailto:info@yursat.com.tr) e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi i¼in +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz.  
**Byk Gardner** Markası, tedarik s¼resi i¼in l¼tfen bizimle iletiŐime ge¼iniz.

*Firmamız Byk Gardner T¼rkiye Distrib¼t¼r¼ veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen ¼r¼nlerde sadece Orjinal ve yeni ¼r¼n teklifi sunmaktadır. Bu sitede g¼sterilen ¼zel marka adları ve ticari markalar ilgili sahiplerinin m¼lkiyetindedir, talep durumunda kaldırılmaktadır.*



¼r¼n	A¼ıklama
<a href="#">5710 Cylindrical Mandrel Bending</a>	
<a href="#">0213</a>	
<a href="#">1130 ISO Cup L</a>	
<a href="#">1511</a>	
<a href="#">16407</a>	
<a href="#">1710 LEITFAHIGKEIT ROHRSONDE, LC2</a>	
<a href="#">1712 LEITFAHIGKEITS PLATTENSONDE, LC2</a>	
<a href="#">1722</a>	
<a href="#">20°;60°;85°</a>	
<a href="#">3122</a>	

<a href="#">3319</a>
<a href="#">3420</a>
<a href="#">3423</a>
<a href="#">4431</a>
<a href="#">4452</a>
<a href="#">4520</a>
<a href="#">4563</a>
<a href="#">4567</a>
<a href="#">4775</a>
<a href="#">5125</a>
<a href="#">5813</a>
<a href="#">6047</a>
<a href="#">6048</a>
<a href="#">6801</a>
<a href="#">6834</a>
<a href="#">6836</a>
<a href="#">7030</a>
<a href="#">70751</a>
<a href="#">74001</a>
<a href="#">9658</a>
<a href="#">Art.No. 1713</a>
<a href="#">Byko test 8500</a>
<a href="#">byko-chart2855</a>
<a href="#">BYKO-TEST 4500 FE/NFE</a>
<a href="#">CD 6836</a>
<a href="#">CD-6834</a>
<a href="#">LCM IV</a>
<a href="#">Mac I</a>
<a href="#">P/N: 5122</a>
<a href="#">P121-10N, Car.N:5015</a>

<a href="#">PV 0573</a>	
<a href="#">PV-0610</a>	
<a href="#">PW-1713</a>	
<a href="#">PW-1722</a>	
<a href="#">SPACER FOR PW-1712</a>	
<a href="#">TIP FOR 5128</a>	
<a href="#">TRI AG-4446</a>	
<a href="#">P/N: CD-6834</a>	
<a href="#">5215</a>	
<a href="#">5126</a>	
<a href="#">4446 Micro-Tri-Gloss</a>	
<a href="#">5810</a>	
<a href="#">107304840</a>	
<a href="#">4442</a>	
<a href="#">3421</a>	
<a href="#">60° Micro-Gloss</a>	Glossmeter
<a href="#">0425</a>	Robust tripod, flow cup
<a href="#">5 4 1 1</a>	
<a href="#">1713 Abstandshalter Fur Pw-1712, 100 Stk.</a>	
<a href="#">107204840</a>	
<a href="#">4504</a>	
<a href="#">107103423</a>	
<a href="#">0214</a>	
<a href="#">Micro Tri Gloss 20-60-85°</a>	Brightness measurement device
<a href="#">4452 Micro-Tri-Gloss S</a>	
<a href="#">Spectro-Guide 45/0 Gloss</a>	portable colorimeter with integrated gloss measurement Delivery: spectrophotometer Calibration standard black Calibration standard white with certificate Test standard green Glossy Standard sample area Software easy-link Interface cable USB adapter 4 alkaline batteries hand strap carrying case operation manual Leaflet color theory
<a href="#">4520 - Obsolete, Possible Replacement 4446</a>	

<a href="#">3635</a>	
<a href="#">Spectro-Quide 45/0 Gloss</a>	
<a href="#">4446</a>	
<a href="#">100804004</a>	
<a href="#">1710 Leitfã196;Higkeit Rohrsonde, Lc2</a>	
<a href="#">3419</a>	
<a href="#">1512</a>	
<a href="#">1712 Leitfã196;Higkeits Plattensonde, Lc2</a>	
<a href="#">5133</a>	
<a href="#">0174</a>	
<a href="#">4840</a>	
<a href="#">5122</a>	
<a href="#">250014276</a>	
<a href="#">3121</a>	
<a href="#">0176 Ford Becher Nr. 4</a>	
<a href="#">5313 (Uretici Kodu 5400 )</a>	
<a href="#">4840 Wave-Scan Dual</a>	
<a href="#">3422</a>	
<a href="#">4561</a>	NEW micro-gloss 60 ° Glossmeter with 60 ° geometry now with brilliant color display and smart-lab software Delivery: glossmeter Quiver with integrated calibration standard Traceable certificate USB cable Software smart-lab Gloss via Download operating manual battery carrying case
<a href="#">20;;60;;85;</a>	
<a href="#">45;/ -Gloss</a>	