

## Cameron

Garanti: 12 ay  
Bu ¼r¼ne ait T¼rkiye i¼i kapı teslim fiyat ve teslim s¼resi i¼eren teklifimizi almak i¼in **info@yursat.com.tr** e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi i¼in +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz.  
**Cameron** Markası, tedarik s¼resi i¼in l¼tfen bizimle iletiŐime ge¼iniz.

*Firmamız Cameron T¼rkiye Distrib¼t¼r¼ veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen ¼r¼nlerde sadece Orjinal ve yeni ¼r¼n teklifi sunmaktadır. Bu sitede g¼sterilen ¼zel marka adları ve ticari markalar ilgili sahiplerinin m¼lkiyetindedir, talep durumunda kaldırılmaktadır.*



¼r¼n	A¼ıklama
<a href="#">4. COMPRESSOR ACTUATOR NO:AAP1800.535-0001</a>	FOR INLET VALVE STAGE 1 AND STAGE 2 SL.NO:CB-15304 MODEL:TAE+55M 4R2 RCD130.—01 No's( Common for both actuator)
<a href="#">5. COMPRESSOR ACTUATOR NO:AAP0540008-01205</a>	FOR BY-PASS VALVE OF Process -1, . SL.NO:CB-15304 MODEL:TAE+55M 4R2 RCD130.—01 No's
<a href="#">6. COMPRESSOR ACTUATOR NO:AAP0540008-01206</a>	FOR BY-PASS VALVE OF Process -2, SL.NO:CB-15304 MODEL:TAE+55M 4R2 RCD130.---01 No's
<a href="#">Demco 4" DM5000 Series Replacement Seat</a>	Part No J002207-021
<a href="#">Demco 2" DM5000 Series Replacement Seat</a>	Part No J001876-011
<a href="#">Nuflo 2" WECO 150 Liquid Flow Meter</a>	Connection Type: 1502 WECO Thread to Thread Connection Size: 2" Bore Size / Flow Rate: 2", 40 - 400USGPM. Pressure Rating: 15000psi Body Material: A286 Stainless Steel Rotor Material: CD4MCU Internals/Bearings: Standard Design Temperature: -20 Deg F to 250 Deg F CSA Explosion Proof
<a href="#">Calibration Certificate for above meter</a>	

<a href="#">100002077</a>	Model 3030AN Magnetic Pick-up for above meter
<a href="#">100003474</a>	Calibrated Redress Kit for 2" Meter above
<a href="#">Calibration Certificate for Redress kit</a>	
<a href="#">VALVE 1/2INCH AIR EJECTOR CAMERON ITS-32</a>	
<a href="#">TA3000</a>	
<a href="#">TA 6000 EJECTOR FILTER</a>	
<a href="#">TA 6000 TA 2000 AIR FILTER</a>	
<a href="#">9A-10101231</a>	NUFLO Liquid 2" 1502 Weco Meter Fluid Type: Liquid End Connection Type: [W1] 1502 Weco – Wing to Thread Series: [NF] NuFlo Certification: PED / ATEX / IECEx Model / Bore Size / Flowrate: [L02] 2", 40-400 USGPM End Connection Size: 2" Body Material: A286 Pressure Rating: 1500 PSI (103.4 Mpa) Rotor Material: CD4MCU Internals / Bearings: Standard Linearity (Grade): +/- 1.00% Conduit Connections: 2 @ 180 Degrees Design Temperature Range: -20 F to 450 F Brazing Option: Brazed Plating Option: Nitrided Documentation / Reports: Material Test Report Hydrostatic Test Chart, 10 min. Flow Test Certificate Flow Curve
<a href="#">2296695-01</a>	Certification: II 2 GD Ex d II T6 Gb Ta = -40C to +70C10203 Ex tD A21 IP6X T85 Connection: (2) ¾" NPT Female Conduit Openings. Power: D-Size Lithium Battery, Main or Backup Power (Included) Externally Supplied 6.0 to 30 VDC Loop Powered (4 to 20mA Output) Outputs: 4 to 20 mA Rate, 8.0 to 30 VDC Required Volumetric Pulse Output, Isolated 60 mA Max @ 50 VDC RS-485 Communications, Baud Range 300 to 115.2K Amp & Square Flowmeter Frequency, Open-Drain Transistor, 50 mA @ 30 VDC Inputs: Turbine Meter Input, Adjustable Sensitivity, 0 to 3500 Hz Remote Reset Input, Isolated, 3.0 to 30 VDC Pulse Input, Isolated, 3.0 to 30 VDC Displays: 8 Digit LCD Total Display BBL 6 Digit LCD Rate Display BPD Totalizer Increments and Flow Rate, Units to be Specified Logging: 384 Daily Logs 768 Hourly Logs 345 Event Logs Communication Protocols: RTU- Mode Modbus Enron Modbus Interface Software (Included): Configuration to Include Multi-Point and Gas Calibration Real Time Data Downloads of Reports, Charts Exports to .XLS and CSV Contains 9A-90099000 Lithium Battery
<a href="#">Calibration / Material Certificates</a>	
<a href="#">P0540016-00074</a>	
<a href="#">9a50179024</a>	CIRCUIT BOARD
<a href="#">9a-100002077, Msi Pc51-16e</a>	
<a href="#">044431-01</a>	
<a href="#">Nuflo Flow Meter Rf 3</a>	

<a href="#">9a-100005135</a>	
<a href="#">Ta-6000(50)(1100/150)</a>	
<a href="#">00003</a>	
<a href="#">Injector Filter For Ta 2000</a>	
<a href="#">Cp2b</a>	COUNTER
<a href="#">Sku 14026335984</a>	
<a href="#">Model 242 E</a>	
<a href="#">Cd -20 A Volt : 230vac</a>	
<a href="#">Model: 256</a>	
<a href="#">201073302</a>	KIT
<a href="#">01233 P 1401435</a>	
<a href="#">Sku 14011470022</a>	
<a href="#">20400</a>	SPRING
<a href="#">Cd -20 A Volt : 110vac</a>	
<a href="#">9a-100079965 S/N 3sbf17727</a>	
<a href="#">9a-100015379</a>	
<a href="#">044351-01</a>	
<a href="#">201073303</a>	REBUILD KIT
<a href="#">2197012-83</a>	
<a href="#">Mb 796039-00003</a>	
<a href="#">6449090370</a>	REBUILD KIT
<a href="#">9a-100005136</a>	
<a href="#">9a-100062996 S/N 4sbf12518</a>	
<a href="#">202ebstsblrdnn03</a>	RECORDER
<a href="#">6818030099</a>	POPPET
<a href="#">Model 202 E</a>	
<a href="#">216485304</a>	PART
<a href="#">288a, 288c</a>	
<a href="#">619012-89-01</a>	
<a href="#">Mb796039-004</a>	
<a href="#">223183101</a>	HEAD

<a href="#">9a-30099004,7,2vdc,</a>	
<a href="#">223183001</a>	UNIT
<a href="#">681801</a>	SEAT
<a href="#">619012-03-06-96</a>	
<a href="#">Aap1404040-00217</a>	
<a href="#">271193308</a>	
<a href="#">6818020099</a>	SEAT
<a href="#">Sor 9ba-Kb45-N4-F1a-9a</a>	
<a href="#">602153-01</a>	
<a href="#">044437-01</a>	
<a href="#">9a-30099004</a>	
<a href="#">Ze544-002a-220</a>	INTERFACE CARD 32CHANNEL DIGITAL OUTPUT
<a href="#">Aamb796039-00004</a>	
<a href="#">044974-02</a>	
<a href="#">9a-100003474</a>	
<a href="#">216434702</a>	CYLINDER
<a href="#">Ze544-005a-840</a>	DISPLAY MODULE 16BUTTON LED RED