

## Casella

Garanti: 12 ay  
Bu ¼r¼ne ait T¼rkiye i¼i kapı teslim fiyat ve teslim s¼resi i¼eren teklifimizi almak i¼in **info@yursat.com.tr** e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi i¼in +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz.  
**Casella** Markası, tedarik s¼resi i¼in l¼tfen bizimle iletiŐime ge¼iniz.

*Firmamız Casella T¼rkiye Distrib¼t¼r¼ veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen ¼r¼nlerde sadece Orjinal ve yeni ¼r¼n teklifi sunmaktadır. Bu sitede g¼sterilen ¼zel marka adları ve ticari markalar ilgili sahiplerinin m¼lkiyetindedir, talep durumunda kaldırılmaktadır.*



¼r¼n	A¼ıklama
<a href="#">Apex2is Standart</a>	Art. Nr.: 48908 Apex2 series Pumps for air sampling Intrinsic safety (IECEX) for use in highly flammable environments Degree of protection IP65 Very comfortable to wear Motion sensor for monitoring the wearer keylock Bluetooth® and Airwave app (Airwave available for free in the Apple App Store and Google Play Store) Compliant with ISO13137 Intrinsically safe pump with motion sensor Scope of delivery: - 1 m hose - protective cover - Quick start Guide
<a href="#">Apex2is Plus</a>	Art. Nr.: 48906 Intrinsically safe pump with motion sensor, Bluetooth®, Data storage, input pressure sensor, runtime timer
<a href="#">Apex2is Pro</a>	Art. Nr.: 48909 Intrinsically safe pump with motion sensor, Bluetooth®, Data storage, inlet pressure sensor, fully programmable Timer, throughput and motion detection.
<a href="#">Art. Nr.: 48925</a>	Charging station for Apex2IS pumps including network
<a href="#">Art. Nr.: 489..</a>	5-station charging station for Apex2IS pumps including power supply
<a href="#">Art. Nr.: 48920</a>	Starter set Apex2IS pumps

<a href="#">M109014</a>
<a href="#">M115002</a>
<a href="#">116000b-01</a>
<a href="#">103750c</a>
<a href="#">M106111</a>
<a href="#">M106110</a>
<a href="#">M128006</a>
<a href="#">M106109</a>
<a href="#">M106113</a>
<a href="#">M106202</a>
<a href="#">M106204</a>
<a href="#">M128002</a>
<a href="#">M112065</a>
<a href="#">142009c</a>
<a href="#">W6 0724</a>
<a href="#">120455a</a>
<a href="#">M106001</a>
<a href="#">Cel-120/1</a>
<a href="#">M106114</a>
<a href="#">M106112</a>
<a href="#">M113011</a>
<a href="#">M110002</a>
<a href="#">M128003</a>
<a href="#">M106108</a>
<a href="#">M128005</a>
<a href="#">SI-240-K1</a>
<a href="#">M106107</a>
<a href="#">M101009</a>
<a href="#">142007d</a>
<a href="#">Cel-120/2</a>

<a href="#">Cel-450</a>
<a href="#">M114029</a>
<a href="#">M128004</a>
<a href="#">M114001</a>
<a href="#">Wbgt</a>
<a href="#">Cel-490</a>
<a href="#">M109015</a>