



Fujikura

Garanti: 12 ay
Bu rne ait Trkiye ii kapı teslim fiyat ve teslim sresi ieren teklifimizi almak iin info@yursat.com.tr e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi iin +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz. **Fujikura** Markası, tedarik sresi iin ltfen bizimle iletiŐime geiniz.

Firmamız Fujikura Trkiye Distribtr veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen rnlerde sadece Orjinal ve yeni rn teklifi sunmaktadır. Bu sitede gsterilen zel marka adları ve ticari markalar ilgili sahiplerinin mlkiyetindedir, talep durumunda kaldırılmaktadır.

CM10-R10P-D(D7) FUJIKURA (DDK Electronics) | ElectroShield

| rn | Aıklama |
|----------------------------|---|
| SP90S-PLUS | Fujikura splice station 90S + / CT50 1) Splicer 90S + 2) Internal battery (BTR-15) 3) AC adapter (ADC-20) and AC power cord (ACC-15) 4) Transport case (CC-39) 5) Work table with tool drawers 6) 1 pair of spare electrodes (ELCT2-16B), alcohol container (AP-02), 3-hole stripping tool (SS03), Fiber holder holder (SP03) 7) Operating instructions 90S + (German) & brief operating instructions 8) CT50 fiberglass separator including fiber clamp & fiber residue container 9) Operating instructions CT50 (German) Detailed information: see data sheet consisting of each 90S-PLUS 90S + Fujikura splicer Lot number |

| | |
|---|---|
| | 85158090 CT50 Fujikura fiber optic separator Lot number 84649000 German user manual 90S +, A6 paper format OPERATING INSTRUCTIONS 90S + |
| SP90S KOMFORTSET | The convenience set is used to optimize work processes and thus productivity. It includes brackets for a splice cassette and a splice protection press, as well as the Splice protection press as such. consisting of each Splice protection press for crimp splice protection Lot number 39269097 Splice protection press 1 pc Mounting bracket set for Fujikura 90S (+) Lot number 76169990 OPT-H90- |
| TOOL SET BASIC | Tool set for Fujikura splice station consisting of each Kevlar scissors with serrated edge and break notch Lot number 82130000 Kevlar scissors 1 pc Tube cutter, IDEAL, gray Lot number 82032000 LTC-02 1 pc Huby chopsticks made of cotton Lot number 56012190 BB-002 4 pack lint-free cleaning cloths for fibers, PU: 90 pcs Lot number 48189090 FW-01 1 PU Stripping tool from 250 or 200µm to 125µm Lot number 82032000 FO 103-S |
| Mass Fusion Splicer 41R Kit | https://www.fusionsplicer.fujikura.com/products/mass-fusion-splicer-41r-kit/ |
| Mass Fusion Splicer 90R Kit | https://www.fusionsplicer.fujikura.com/products/mass-fusion-splicer-90r-kit-series-e/ |
| FCX-MWL-F-AC-CH | PM - 16 2021 4711 FCX-MWL series FCX-MWL-F-AC-CH oxygen module Item description: 0.1...95% oxygen 0...950mVDC lin. Sensor with flow housing Old article designation before 04/01/2018: 103-12-102-0241 |
| FH-100-900 | FSM100 fiber holder for fibers with 890-1000µm coating |
| SP90S-PLUS | Fujikura splice box 90S+ / CT50 Scope of delivery: 1) Splicer 90S+ 2) Internal Battery (BTR-15) 3) AC Adapter (ADC-20) and AC Power Cord (ACC-15) 4) Transport case (CC-39) 5) Work table with tool drawers 6) 1 pair of spare electrodes (ELCT2-16B), alcohol canister (AP-02), 3 hole stripping tool (SS03), Fiber holder mount (SP03) 7) Operating instructions 90S+ (German) & short operating instructions 8) CT50 fiber optic cleaver including fiber clip & fiber scrap container 9) Operating Instructions CT50 (German) consisting of each 90S+ Fujikura splicer Lot number 85158090 90S-PLUS 1 pc Fujikura fiber optic cleaver Commodity number 84649000 CT50 1 pc German operating instructions 90S+, A6 paper format INSTRUCTION MANUAL 90S+ 1 pc |
| SP90S COMFORT SET | Accessory set for splice space 90S(+) & CT50 |
| TOOL SET BASIC | Tool set for Fujikura splice box |
| 70S+ | |
| SP41S-PLUS | Fujikura splice box 41S-PLUS / CT50 Description: Splice station with a particularly small, light, handy and fully automatic arc splicer 41S-PLUS for multimode and singlemode fibers, application in particular for the production of FTTH connections and work in the LAN and campus area. Fiber positioning via active V-groove alignment (in three axes) and control with 2 CCD cameras, 5.0 inch color screen, easy processing and insertion of the fibers using the fiber holder system. Memory for 10,000 splice results. NEW*: <input type="checkbox"/> Active Fusion Control technology <input type="checkbox"/> Active Blade Management Technology Scope of delivery: Splicer 41S-PLUS (2-year guarantee with annual maintenance), BTR-11 rechargeable battery, external power pack/charger ADC-19A, mains cable ACC-11, Clamp-S31A, 1 pair of spare electrodes ELCT2-16B (5000 splices), transport case CC - 36, fiber cleaver CT50 with fiber holder, 3 hole stripping tool (SS03), alcohol container (AP-02), fiber holder receiver (SP-01) Optional accessories: 1 pair each FH-70-250 fiber holder FH-70-900 fiber holder FH-FC-20 (900µm core in 2mm cable) FH-FC-30 (900µm core in 3mm cable) Clamp-S31B fiber clamp for 0.9mm loose tube cores FH-60-LT900 fiber holder for 0.9mm loose tube cores consisting of each Fujikura splicer 41S-PLUS Lot number 85158090 41S-PLUS 1 pc Fujikura fiber optic cleaver Commodity number 84649000 |

| | |
|---|--|
| OPT-STATIV-ES | Tripod for 90S+/41S+ & NanoFlow MAX Professional tripod incl. extra wide quick-change adapter (incl. 1/4" & 3/8" screw) for a stable fixation. Thanks to the infinitely adjustable legs, working on uneven surfaces is no problem. Usable for Fujikura 90S/+, 41S/+, Fremco NanoFlow /MAX Tripod height: 160.5 cm / weight including adapter: 2 kg |
| TOOL SET BASIC | Tool set for Fujikura splice box Kevlar scissors 1 pc Loose tube cutter, IDEAL, grey Commodity number 82032000 LTC-02 1 pc Huby cotton chopsticks Commodity number 56012190 BB-002 4 Pack Lint-free cleaning cloths for fibers, PU: 90 pcs Lot number 48189090 FW-01 1 pack Stripping tool from 250 or 200µm to 125µm Commodity number 82032000 |
| SP90S-PLUS | Fujikura splice box 90S+ / CT50 Scope of delivery: 1) Splicer 90S+ 2) Internal Battery (BTR-15) 3) AC Adapter (ADC-20) and AC Power Cord (ACC-15) 4) Transport case (CC-39) 5) Work table with tool drawers 6) 1 pair of spare electrodes (ELCT2-16B), alcohol canister (AP-02), 3 hole stripping tool (SS03), Fiber holder mount (SP03) 7) Operating instructions 90S+ (German) & short operating instructions 8) CT50 fiber optic cleaver including fiber clip & fiber scrap container 9) Operating Instructions CT50 (German) consisting of each 90S-PLUS 1pc. 90S+ Fujikura splicer CT50 1 pc Fujikura fiber optic cleaver German operating instructions 90S+, A5 paper format INSTRUCTION MANUAL 90S+ 1 pc |
| CT08 | Fujikura fiber optic cleaver with fiber plate Commodity number 84649000 Standard set cleave length 5 - 20m |
| Fiber optik pigtail (SC connector) | |
| FSM-40S A SM MM Fusion Splicer w/ Cleaver | |
| SP90S-PLUS | Splice space 90S+ / CT50 Scope of delivery: 1) Splicer 90S+ 2) Internal Battery (BTR-15) 3) AC Adapter (ADC-20) and AC Power Cord (ACC-15) 4) Transport Case (CC-39) 5) Work table with tool drawers 6) 1 pair of spare electrodes (ELCT2-16B), alcohol canister (AP-02), 3 hole stripping tool (SS03), Fiber holder mount (SP03) 7) Operating instructions 90S+ (German) & short operating instructions 8) CT50 fiber optic cleaver including fiber clip & fiber scrap container 9) Operating Instructions CT50 (German) consisting of each 90S+ Fujikura splicer Lot number 85158090 90S-PLUS 1 pc Fujikura fiber optic cleaver Commodity number 84649000 CT50 1 pc German operating instructions 90S+, A5 paper format Commodity number 49011000 INSTRUCTION MANUAL 90S+ 1 pc |
| ELCT2-16B | 90S(-PLUS)/41S/31S |
| XFPM-200KPG Pressure Sensor (Gauge Type), 4.5V, | |
| AFL-JP-06-TH | |
| FH-70-250 | |
| FH-60-250 | |
| FH-70-900 | |
| FH-60-900 | |
| AFL S014773 | |
| XFPM-200KPG Pressure Sensor (Gauge Type), 4.5V, | |
| CT50 | Fiber optic separator Single-action: opening, cocking and transporting are 1 process. Wide opening device allows easy fiber insertion. Automatic cutting blade adjustment possible via Bluetooth from the splicer. Blade life up to 60,000 breaks (3 heights x 16 positions) For single fibers or fiber ribbons with up to 12 fibers - including Fiber Plate |

| |
|---|
| AD-10-M24 - including 2x AAA batteries - including screw for bracket (OPT-H70-CT50-RS) |
| Annual Inspection Of L/Raft Type:Fm -Sv-15r,Cap:15person Serial No: Svr150883 |
| Annual Inspection Of L/Raft Type:Fm A-20h,Cap:20person Serial No: H205001 |
| Adc-13 |
| SP90S-PLUS// 90S+ / CT50 1) Splicer 90S+ 2) Internal Battery (BTR-15) 3) AC Adapter (ADC-20) and AC Power Cord (ACC-15) 4) Transport Case (CC-39) 5) Work table with tool drawers 6) 1 pair of spare electrodes (ELCT2-16B), alcohol canister (AP-02), 3 hole stripping tool (SS03), Fiber holder mount (SP03) 7) Operating instructions 90S+ (German) & short operating instructions 8) CT50 fiber optic cleaver including fiber clip & fiber scrap container 9) Operating Instructions CT50 (German) |
| 70 S |
| Fwd:- Sr. No. Svr60718 / Type: Fm-Sv-6rs / Capacity: 6 Person |
| Acc-11 For Fsr-02 |
| 70s/80s |
| 8522 Xfpm-050kpgpt |
| 50s Splice Tool Battery |
| 80s Maximum Complectation |
| Cm10 – R10p – D (D7) |
| Adc-09 |
| Adc-10 For Fsr-02 |
| 60s Kit |
| 40s Fusion Splicer |
| 1.5d-Qew |
| Adc-11 |
| 60s Or 70s Depend Of The Price |
| Stbd:- Sr. No. Svr251145 / Type: Fm-Sv-25rs / Capacity: 25 Person |
| 70s/S015591 |
| 60 S Obsolete Replaced By 70s |
| Annual Inspection Of L/Raft Type:Fm -Sa-10h,Cap:10person Serial No: Sa100153 |
| Fms-80s Fiber |
| 62s Fusion Splicer |
| 1.5d-Hqew |
| 22s |
| Port:- Sr. No. Svr251146 / Type: Fm-Sv-25rs / Capacity: 25 Person |

[60s \(Obsolete - Replaced By S015591\) Splice Machine](#)

[Websp2116m-1-D](#)