

## Qualitrol



Garanti: 12 ay

Bu rne ait Trkiye ii kapı teslim fiyat ve teslim sresi ieren teklifimizi almak iin [info@yursat.com.tr](mailto:info@yursat.com.tr) e-posta adresine baŐvuru yapabilir ya da ayrıntılı bilgi iin +90 224 240 03 04 numaralı telefonumuzdan bizlere ulaŐabilirsiniz.

**Qualitrol** Markası, tedarik sresi iin ltfen bizimle iletiŐime geiniz.

*Firmamız Qualitrol Trkiye Distribtr veya temsilcisi deĐildir. Firmamız sipariŐ durumunda, belirtilen rnlerde sadece Orjinal ve yeni rn teklifi sunmaktadır. Bu sitede gsterilen zel marka adları ve ticari markalar ilgili sahiplerinin mlkiyetindedir, talep durumunda kaldırılmaktadır.*

rn	Aıklama
<a href="#">Cas-664-1</a>	3.5 GAGE CASE ASBY
<a href="#">AKM35-WTI</a>	MV Winding temperature indicator
<a href="#">AKM34-OTI</a>	Oil temperature indicator
<a href="#">Pressure relief device LRPD</a>	
<a href="#">AKM345-00404665 OIL TEMP/WINDING TEMP INDICATOR</a>	
<a href="#">AKM345-00404010 AKM345</a>	Winding Temperature Indicator, Gen3, Standard Temp Range
<a href="#">PRODUCT ID : S-782504</a>	COMPOUND PRESSURE GAUGE MODEL : 50-35E
<a href="#">AKM 44712 level oil indicator</a>	
<a href="#">900-003-02 1.7 bar</a>	
<a href="#">Seal-in Relay 909-300-02</a>	
<a href="#">34/Gen2.6.00.TD111.10 (OTI)</a>	
<a href="#">35/Gen2.TD76.6.01.EB111.10 (WTI)</a>	
<a href="#">44650-05 WINDING TEMP INDICATOR C.N.01092</a>	
<a href="#">44650-05 WINDING TEMP INDICATOR C.N.01092</a>	
<a href="#">909-200-01, Seal-in relay for SPR</a>	
<a href="#">015-002-01</a>	
	MEASURING RANGE: 0 - 150 DEG C TYPE: WINDING TEMPERATURE INDICATOR DISPLAY TYPE: ANALOG MATERIAL COLOR: RAL 7000-C5H MOUNTING TYPE: STANDARD MOUNTING,CERTIFICATION/STANDARD: MEASURING

<a href="#">AKM345-00405840 GEN 3</a>	ACCURACY +/- 2% FSD PROTECTION CLASS: IP66 ADDITIONAL INFO: THERMOMETER STYLE 35 WTI/GEN3 PROBE TYPE: 18 CAPILLARY LENGTH: 16 MT. LENS MATERIAL: GLASS CABLE ENTRY: M20 & M25 NUMBER OF SWITCH: 6
<a href="#">208-030-03 PRD 12 PSI W/DPDT SWITCH</a>	
<a href="#">CAS-664-1 3.5 GAGE CASE ASBY</a>	
<a href="#">CON000-00194006 DETACHABLE CONNECTOR ASSEMBLY</a>	
<a href="#">108-018-01</a>	TEMP MONITOR
<a href="#">Prd 208-015-03 10 Psi</a>	
<a href="#">Llg032-00143601</a>	
<a href="#">91001505</a>	RELAY
<a href="#">032-048-01</a>	
<a href="#">Akm345-00016717</a>	
<a href="#">042-300-02</a>	
<a href="#">9348-0005</a>	
<a href="#">Akm 67</a>	
<a href="#">148-008-01</a>	PV SW GAGE ASBY
<a href="#">Akm345-00272788</a>	
<a href="#">092-300-01</a>	
<a href="#">04501401</a>	GAUGE
<a href="#">050 35e</a>	
<a href="#">Itm509-00273630</a>	
<a href="#">118itmp4</a>	MONITOR
<a href="#">900-009-01</a>	RAPID PRESSURE RISE RELAY
<a href="#">042 334 05</a>	
<a href="#">118p120k42</a>	MONITOR
<a href="#">03 02 25</a>	
<a href="#">900-003-32</a>	
<a href="#">Tr6000-00022175</a>	
<a href="#">900-016-01 (Obsolete Replaced By 900- 016-02)</a>	

<a href="#">104-680-02</a>	6 RMT MT WND
<a href="#">34.5/0.69kv Manometre</a>	
<a href="#">Lprd00-00006254</a>	
<a href="#">9039-0010</a>	CPU CARD IDM T2
<a href="#">118I 3 P X X</a>	
<a href="#">208-007-02</a>	
<a href="#">13-9501-03-004</a>	
<a href="#">208-001-40 Prd 10 Psi</a>	
<a href="#">909-210-01</a>	RELAY SEAL-IN FOR POWER TRANSFORMER
<a href="#">38960-3</a>	
<a href="#">Akm345-00237354</a>	
<a href="#">Ap-C10-01a-01e_092</a>	
<a href="#">205 012 01</a>	
<a href="#">80-9264-07</a>	MKIII LOCAL STORAGE UNIT 80GB HD
<a href="#">125t</a>	
<a href="#">Con000-00273484</a>	
<a href="#">20800710</a>	PRESSURE VALVE
<a href="#">900-025-01</a>	
<a href="#">As1000 00193249</a>	
<a href="#">Akm345-00253395</a>	
<a href="#">Akm34500036688</a>	TEMP INDICATOR
<a href="#">T/Guard 405 System</a>	
<a href="#">Idm-T2-Idm-Dau-Dfro-U/G</a>	UPGRADE KIT IDM DFR
<a href="#">Akm Olr</a>	
<a href="#">Akm 35</a>	
<a href="#">104-412-01</a>	
<a href="#">Ap-L17-03I-01e_049</a>	
<a href="#">Cab 625 4</a>	
<a href="#">Akm345 00237158</a>	
<a href="#">900/910</a>	

<a href="#">Akm Oti Type 34</a>	
<a href="#">20800704</a>	PRESSURE VALVE
<a href="#">Plt-719-1 900/910</a>	
<a href="#">Con 630 3</a>	
<a href="#">104-317-01</a>	LIQUID TEMPERATURE GAUAGE
<a href="#">10433201</a>	THERMOSTAT
<a href="#">031-036-01 Cs-33018</a>	
<a href="#">Con-659-13</a>	
<a href="#">Es25430001-001</a>	
<a href="#">Sbu80-302</a>	
<a href="#">104-673-03 Cs-34413</a>	6 REMOTE MT THERMO 4SW 180C
<a href="#">261d339g01</a>	
<a href="#">042-017-01</a>	
<a href="#">003 30p</a>	
<a href="#">118p12k01</a>	PANEL
<a href="#">10432101</a>	TEMP INDICATOR
<a href="#">208-030-03</a>	
<a href="#">092-051-01</a>	
<a href="#">Etm505-00033438</a>	
<a href="#">118h U K 02</a>	
<a href="#">Idm-T2-Mkii-Anl</a>	IDM T2 ANALOG CARD
<a href="#">042-012-01</a>	
<a href="#">206 Mprd</a>	
<a href="#">148-018-01 Cs-45471</a>	
<a href="#">Lprd00-00256811</a>	
<a href="#">13-9498-05-008</a>	
<a href="#">208-60v</a>	
<a href="#">030 062 01</a>	
<a href="#">48515 1</a>	
<a href="#">039-014-01 Cs-40164</a>	
<a href="#">9073-0003</a>	

<a href="#">104-324-28</a>	
<a href="#">Xprd00-00032658</a>	XTRA PROTECTION
<a href="#">Tt0e94mva</a>	
<a href="#">Akm345 00245975</a>	
<a href="#">909-300-01</a>	RELAY AC/DC SEAL IN FOR POWER TRANSFORMER
<a href="#">900-009-03</a>	RAPID PRESSURE RISE FLG Q W/VNT
<a href="#">Akm345-00094319</a>	
<a href="#">Ied50900026617</a>	TEMP CONTROL
<a href="#">90930002</a>	CONTROL MODULE
<a href="#">Llg042-00260330</a>	
<a href="#">208-007-05</a>	
<a href="#">118p-U-K-0-1</a>	DIGITAL TEMPERATURE MONITOR 3-DIGIT LCD DISPLAY
<a href="#">038</a>	
<a href="#">032-301-02 G1081 !! By Llg032-00143601</a>	
<a href="#">208 60aj C5 32027</a>	
<a href="#">T/Guard 405, 16</a>	
<a href="#">Tr6000b-00176476</a>	
<a href="#">Swt-645-1</a>	
<a href="#">Akm345-00271331</a>	
<a href="#">109-119-02</a>	TEMPERATURE MONITOR ELECTRONIC
<a href="#">050-35e</a>	
<a href="#">Cas-664-1 Flow Indicator</a>	
<a href="#">900-016-02</a>	
<a href="#">35650-150/150</a>	
<a href="#">9193-0005</a>	
<a href="#">9040-0007</a>	ANALOG CARD IDM T2
<a href="#">050 010 01</a>	
<a href="#">38920 3</a>	
<a href="#">Ied509 00244662</a>	

<a href="#">202-030-01n</a>	PR VALVE 10 PSI
<a href="#">E-Lok Br151/140</a>	
<a href="#">Wtf-1030-1</a>	THERMAL PLATE TP:WTF-F-T/R-1 ENG
<a href="#">118itm P 4 M</a>	
<a href="#">Ext-3mp-10</a>	
<a href="#">910-014-02</a>	
<a href="#">031 102 07 Cs 40160</a>	
<a href="#">148 010 01</a>	
<a href="#">900 003 02</a>	
<a href="#">Akm345 00243386</a>	
<a href="#">Idm-T2-Mkii-Cpu</a>	IDM T2 CPU CARD
<a href="#">Ben 6000</a>	
<a href="#">Llg042-00014409</a>	
<a href="#">104 328 01</a>	
<a href="#">20860s</a>	PRESSURE VALVE
<a href="#">22-9449-06</a>	
<a href="#">909-300-01 Ac-Dc</a>	
<a href="#">91001106</a>	PRESSURE GAUGE
<a href="#">038-002-03</a>	
<a href="#">Akm345-00271332</a>	
<a href="#">Akm34500017656</a>	TEMP INDICATOR
<a href="#">Akm Wti Type 35</a>	
<a href="#">Llg-042-00020590</a>	
<a href="#">148 - 018 - 014 Cs - 45471</a>	
<a href="#">910-010-03</a>	RELAY RAPID PRESSURE RISE
<a href="#">Akm345</a>	
<a href="#">Akm34500228832</a>	TEMP INDICATOR